



LED TWIST RECHARGEABLE INSPECTION LIGHT, 6W COB LED & 1W SMD LED, COLOUR MATCH CRI 96+, 3-COLOUR

MODEL NO: **LED601CM**

Thank you for purchasing a Sealey product. Manufactured to a high standard, this product will, if used according to these instructions, and properly maintained, give you years of trouble free performance.

IMPORTANT: PLEASE READ THESE INSTRUCTIONS CAREFULLY. NOTE THE SAFE OPERATIONAL REQUIREMENTS, WARNINGS & CAUTIONS. USE THE PRODUCT CORRECTLY AND WITH CARE FOR THE PURPOSE FOR WHICH IT IS INTENDED. FAILURE TO DO SO MAY CAUSE DAMAGE AND/OR PERSONAL INJURY AND WILL INVALIDATE THE WARRANTY. KEEP THESE INSTRUCTIONS SAFE FOR FUTURE USE.



Refer to
instructions

1. SAFETY

- ❑ **WARNING!** Inspect the cable and connector for wear and damage to ensure items are safe before connecting to the power supply. If worn or damaged **DO NOT** use.
IMPORTANT: Ensure the lamp is fully charged before initial use.
- ✗ **DO NOT** charge in damp conditions.
- ✗ **DO NOT** turn the lamp on when it is being charged.
- ✗ **DO NOT** shine directly into your, another person's or an animal's eyes. **DO NOT** allow children to use the lamp.
- ✗ **DO NOT** handle or move the lamp whilst it is being charged.
- ✗ **DO NOT** use the lamp if you suspect that the battery or the lamp casing is damaged.
- ✗ **DO NOT** leave battery in a discharged state, recharge battery immediately. Before storage, fully recharge the battery, subsequently recharge the battery at least once every six months of non-use.
- ✗ **DO NOT** attempt to open, disassemble, modify or service the battery pack.
- ✗ **DO NOT** crush, puncture, short external contacts or dispose of in fire or water.
- ✗ **DO NOT** expose to temperatures above 60°C (140°F).
- ✓ Recycle or dispose of used battery as stipulated by local regulation.
- ✓ If the electrolyte in the cells gets on your skin, thoroughly wash with soap and water. If it gets in your eyes, rinse thoroughly with cool water and seek immediate medical attention.

2. INTRODUCTION

Three colour options to choose from: 2700K, 4500K and 6500K at 500 lumens. CRI96+ Colour match suitable for accurate colour matching, detecting swirls and identifying imperfections in bodywork. Features an LED battery level indicator that displays battery status during use and while charging. 3.7V 2.6Ah Lithium-ion battery for extended battery life with a long runtime of 3hrs. Light body twists 360° and light arm tilts 180° to provide light at any angle. Features a swivel hanging hook and rubber covered magnet on the base, which allow hands-free operation.

3. SPECIFICATION

Model No:	LED601CM
Battery:	3.7V 2.6Ah Lithium-ion
Charging Time:	4hr
CRI Rating:	96+
IP Rating:	IP52
Lumen Output:	Side/Top: 500/100lm
Operating Time:	Side/Top: 3/8hr

4. FEATURES

1	Adjustable base
2	Twist adjustment
3	LED charging indicator lights
4	C type charger socket
5	ON/OFF switch
6	Belt clip
7	Hanging hook



The battery fitted to this lamp is considered to be a consumable item and its ability to accept a charge will reduce over time. We will provide warranty against mechanical and electrical defect for a period of one year - this does not cover fair wear and tear. If the battery is not properly charged before first use, or regularly conditioned, its capacity will diminish. Under these circumstances we will not replace the battery regardless of whether the battery is less than one year old.

5. OPERATION

- 5.1. Connect the USB lead to the socket (4) on the side of the lamp. Plug into USB power supply and turn on, the charging LED's on the lamp (3) will flash green to show that charging has commenced.
- 5.2. The number of green lights flashing indicate the level of charge.
- 5.3. When the battery has fully charged all the LED's will show steady green.
- 5.4. Direct the lens away from your eyes before switching on.
- 5.5. Toggle the lamp between light levels using the ON/OFF switch.
- 5.6. The lamp may be suspended by the hanging hook or attached to any ferrous surface by using the magnet on the base.
- 5.7. When the light is hanging from the hook it can be rotated through 360° for more precise positioning.
- 5.8. Rotate the base section to achieve the angle required. When attached to a ferrous surface, using the base magnet, the lamp can be rotated to shine in any direction. See fig.1 for reference.



fig.1



BATTERY REMOVAL

Remove the screws in the black section of the lamp control section to remove the batteries.

Under the Waste Batteries and Accumulators Regulations 2009, Jack Sealey Ltd are required to inform potential purchasers of products containing batteries (as defined within these regulations), that they are registered with Valpak's registered compliance scheme. Jack Sealey Ltd's Batteries Producer Registration Number (BPRN) is BPRN00705.



ENVIRONMENT PROTECTION

Recycle unwanted materials instead of disposing of them as waste. All tools, accessories and packaging should be sorted, taken to a recycling centre and disposed of in a manner which is compatible with the environment. When the product becomes completely unserviceable and requires disposal, drain any fluids (if applicable) into approved containers and dispose of the product and fluids according to local regulations.



REGISTER YOUR PURCHASE HERE



WEEE REGULATIONS

Dispose of this product at the end of its working life in compliance with the EU Directive on Waste Electrical and Electronic Equipment (WEEE). When the product is no longer required, it must be disposed of in an environmentally protective way.

Contact your local solid waste authority for recycling information.

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. Please note that other versions of this product are available. If you require documentation for alternative versions, please email or call our technical team on technical@sealey.co.uk or 01284 757505.

IMPORTANT: No Liability is accepted for incorrect use of this product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which is required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



sales@sealey.co.uk



www.sealey.co.uk