CBR - MASONRY REINFORCEMENT MESH





Provide added strength and stability.

FEATURES

Installation

- All metal components used in any particular application must be of the same material type.
- Gloves should be worn to protect hands from sharp metal edges.
- Position the mesh within the masonry bed joints, providing a minimum of 25 mm cover to external faces.
- Overlap by a minimum of 75 mm if joining two lengths together. The mesh can be laid every third brickwork course for most reinforcement.





TECHNICAL DATA

Product dimensions

References	Material	Dimensions
CBR2063	Galvanised	63mm x 20mm
CBR2063S	Stainless Steel	63mm x 20mm
CBR20112	Galvanised	112mm x 20mm
CBR20112S	Stainless Steel	112mm x 20mm
CBR20175	Galvanised	175mm x 20mm
CBR20175S	Stainless Steel	175mm x 20mm
CBR20228	Galvanised	228mm x 20mm
CBR20228S	Stainless Steel	228mm x 20mm
CBR20305	Galvanised	305mm x 20mm

Technical data sheet

CBR - MASONRY REINFORCEMENT MESH



Winchester Road Cardinal Point Tamworth Staffordshire B78 3HG tel: +44 1827 255600 / fax: +44 1827 255616

CBR - Masonry Reinforcement Mesh

page 2/2